



WORKING DIAGRAM																													
	I = Inlet																												
	O = Outlet																												
	D = Drain																												
	BP = By-Pass																												
<table border="1"> <tbody> <tr> <td>1</td> <td>BODY</td> <td>AISI 316I</td> <td></td> </tr> <tr> <td>2</td> <td>BONNET</td> <td>AISI 316</td> <td></td> </tr> <tr> <td>3</td> <td>PACKING</td> <td>TEFLON</td> <td></td> </tr> <tr> <td>4</td> <td>STEM</td> <td>AISI 316</td> <td></td> </tr> <tr> <td>5</td> <td>NEEDLE</td> <td>AISI 316</td> <td></td> </tr> <tr> <td colspan="2">Working pressure: 420 Bar</td> <td colspan="2">Net weight:</td> </tr> <tr> <td colspan="2">Proof pressure: 630 Bar.</td> <td colspan="2">1.1 Kg</td> </tr> </tbody> </table>		1	BODY	AISI 316I		2	BONNET	AISI 316		3	PACKING	TEFLON		4	STEM	AISI 316		5	NEEDLE	AISI 316		Working pressure: 420 Bar		Net weight:		Proof pressure: 630 Bar.		1.1 Kg	
1	BODY	AISI 316I																											
2	BONNET	AISI 316																											
3	PACKING	TEFLON																											
4	STEM	AISI 316																											
5	NEEDLE	AISI 316																											
Working pressure: 420 Bar		Net weight:																											
Proof pressure: 630 Bar.		1.1 Kg																											

DR0244
AISI 316 Stainless Steel

General tolerance on all the drawing ± 0.1
 Millimetrical measurement except different
 indications